

# Product data sheet

Specifications

SQUARE D



## Non-Reversing Starter Size 0, 2-Pole, Melting Alloy Overload, NEMA 1 +Options

8536SBG1V02A

Price\*: 675.00 USD

! Discontinued

### Main

Product Type	Starter
Product Range	S
Starter Type	Non reversing

### Complementary

Nema Size	0
Rated Current	18 A
Number Of Poles	2P
Maximum Voltage Rating	600 V AC
Phase	1 phase
Type Of Overload	Melting alloy 1
Horsepower Rating	1 HP 115 V AC 2 HP 230 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	2 momentary push-buttons (START-STOP)
Terminal Type	Screw clamp terminals
Height	10.00 in (254 mm)
Width	5.98 in (152 mm)
Depth	5.55 in (141 mm)

### Environment

Enclosure Type	NEMA 1 painted sheet steel
Certifications	NEMA CSA UL Listed

### Ordering and shipping details

Discount Schedule	CP1
Gtin	785901718802
Returnability	No
Country Of Origin	US

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	6.00 lb(US) (2.722 kg)

## Contractual warranty

Warranty	18 months
----------	-----------