

Product data sheet

Specifications

SQUARE D



Non-Reversing Starter Size 0, 2-Pole, Non Compensated Bimetallic, NEMA 1

8536SBG1V02B1CP1X11

! Discontinued

Main

Product Type	Starter
Product Range	S
Starter Type	Non reversing

Complementary

Nema Size	0
Rated Current	18 A
Number Of Poles	2P
Maximum Voltage Rating	600 V AC
Phase	1 phase
Type Of Overload	Non-compensated bimetallic
Horsepower Rating	1 HP 115 V AC 2 HP 230 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator on incandescent
Auxiliary Contacts	1 NO + 1 NC
Terminal Type	Screw clamp terminals

Environment

Enclosure Type	NEMA 1 painted sheet steel
Certifications	CSA UL Listed NEMA

Ordering and shipping details

Category	21191-8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------