

Product data sheet

Characteristics

8536SBG1V84CFF4TX11

Non-Reversing Starter Size 0, 2-Pole, Melting Alloy Overload, NEMA 1 +Options

Price* : 1,686.00 USD



⚠ Discontinued

8536SBG1V84CFF4TX11 has not been replaced.
Please contact your customer care center for more information.

Main

Product or component type	Starter
Type	S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 208 V AC 60 Hz primary circuit
Motor starter type	Non reversing
Line Rated Current	18 A
Number of Poles	2P
Phase	1 phase
Horsepower Rating	1 HP 115 V AC 2 HP 230 V AC
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Auxiliary Contacts	1 NO + 1 NC
Control Circuit Fusing	2 fuses (primary), 1 fuse (secondary)
Thermal overload type	Melting alloy 1 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	0

Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	NEMA CSA UL listed

Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	26.34

Returnability	N
Country of origin	MX

Contractual warranty

Warranty period	18 months
-----------------	-----------
