

# 8536SBG1V89CFF4P1TX20

Non-Reversing Starter Size 0, 2-Pole, Melting Alloy Overload, NEMA 1 +Options

Price\* : 2,024.00 USD



8536SBG1V89CFF4P1TX20 has not been replaced.  
Please contact your customer care center for more information.

⚠ Discontinued

## Main

Product or component type	Starter
Type	S
Control Circuit Type	Control circuit transformer

## Complementary

Control Circuit Voltage	24 V AC 60 Hz secondary circuit 120 V AC 60 Hz primary circuit
Motor starter type	Non reversing
Line Rated Current	18 A
Number of Poles	2P
Phase	1 phase
Horsepower Rating	1 HP 115 V AC 2 HP 230 V AC
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator: on type: incandescent
Auxiliary Contacts	2 NO
Control Circuit Fusing	2 fuses (primary), 1 fuse (secondary)
Thermal overload type	Melting alloy 1 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	0

## Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	UL listed NEMA CSA

## Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1

---

Package weight(Lbs)	26.870000000000001
Returnability	N
Country of origin	MX

---

**Contractual warranty**

---

Warranty period	18 months
-----------------	-----------

---