

# 8536SBG2V02CFF4P1ST

Non-Reversing Starter Size 0, 3-Pole, Melting Alloy Overload, NEMA 1 +Options

Price\* : 1,886.00 USD



⚠ Discontinued

8536SBG2V02CFF4P1ST has not been replaced.  
Please contact your customer care center for more information.

## Main

Product or component type	Starter
Type	S
Control Circuit Type	Control circuit transformer

## Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	18 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator: on type: incandescent
Control Circuit Fusing	2 fuses (primary), 1 fuse (secondary)
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	0

## Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	CSA NEMA UL listed

## Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1

---

Nbr. of units in pkg.	1
Package weight(Lbs)	28.57
Returnability	N

---

**Contractual warranty**

---

Warranty period	18 months
-----------------	-----------

---