

Product data sheet

Specifications

SQUARE D



Non-Reversing Starter Size 0, 3-Pole, Melting Alloy Overload, NEMA 1 +Options

8536SBG2V02CFS

Price*: 1,038.00 USD

! Discontinued

Main

Product Type	Starter
Product Range	S
Starter Type	Non reversing

Complementary

Nema Size	0
Rated Current	18 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Melting alloy 3
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Separate control circuit
Control Units	Selector switch (HAND-OFF-AUTO)
Other Equipment	1 fuse
Terminal Type	Screw clamp terminals
Height	10.00 in (254 mm)
Width	5.98 in (152 mm)
Depth	5.55 in (141 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel
Certifications	CSA UL Listed NEMA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	US
-------------------	----

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	6.00 lb(US) (2.722 kg)

Contractual warranty

Warranty	18 months
----------	-----------