

Product data sheet

Specifications

SQUARE D



Non-Reversing Starter Size 0, 3-Pole, Motor Logic SSOLR (Class 10), NEMA 1

8536SBG2V02CH10P1S

Discontinued

Main

| | |
|---------------|---------------|
| Product Type | Starter |
| Product Range | S |
| Starter Type | Non reversing |

Complementary

| | |
|------------------------|--|
| Nema Size | 0 |
| Rated Current | 18 A |
| Number Of Poles | 3P |
| Maximum Voltage Rating | 600 V AC |
| Phase | 3 phase |
| Type Of Overload | Solid state Motor Logic class 10 |
| Horsepower Rating | 3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC |
| Coil Voltage | 110 V AC 50 Hz 120 V AC 60 Hz |
| Control Circuit Type | Separate control circuit |
| Control Units | Selector switch (HAND-OFF-AUTO) |
| Pilot Light | Red indicator on incandescent |
| Terminal Type | Screw clamp terminals |

Environment

| | |
|----------------|----------------------------|
| Enclosure Type | NEMA 1 painted sheet steel |
| Certifications | NEMA UL Listed CSA |

Ordering and shipping details

| | |
|-------------------|----------------------------------|
| Category | 21191-8502,36 SA,SB(NOT S*R,T,W) |
| Discount Schedule | CP1 |
| Returnability | No |
| Country Of Origin | MX |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

| | |
|------------------------------|------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Weight | 7.00 lb(US) (3.175 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|