

8536SBG2V80CFF4H20P1P2TX11

Non-Reversing Starter Size 0, 3-Pole, Motor Logic
SSOLR (Class 20), NEMA 1

Price** : 2,474.00 USD



8536SBG2V80CFF4H20P1P2TX11 has not been replaced.
Please contact your customer care center for more information.

⚠ Discontinued

Main

Product or component type	Starter
Type	S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	240 V AC 60 Hz primary circuit 120 V AC 60 Hz secondary circuit
Motor starter type	Non reversing
Line Rated Current	18 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator: on type: incandescent Green indicator: off type: incandescent
Auxiliary Contacts	1 NO + 1 NC
Control Circuit Fusing	2 fuses (primary), 1 fuse (secondary)
Thermal overload type	Solid state Motor Logic class 20
Electrical connection	Screw clamp terminals
NEMA size	0

Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	CSA NEMA UL listed

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	27.400000000000002
Returnability	N
Country of origin	MX

Contractual warranty

Warranty period	18 months
-----------------	-----------