


# 8536SCG3V01CH20P1SX10

Non-Reversing Starter Size 1, 3-Pole, Motor Logic  
SSOLR (Class 20), NEMA 1

Price\* : 1,353.00 USD



⚠ Discontinued

8536SCG3V01CH20P1SX10 has not been replaced.  
Please contact your customer care center for more information.

## Main

Product or component type	Starter
Type	S
Control Circuit Type	Separate control circuit

## Complementary

Control Circuit Voltage	24 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	27 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator: on type: incandescent
Auxiliary Contacts	1 NO
Thermal overload type	Solid state Motor Logic class 20
Electrical connection	Screw clamp terminals
NEMA size	1

## Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	CSA UL listed NEMA

## Ordering and shipping details

Category	21192 - 8502,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1

Package weight(Lbs)	8
Returnability	N
Country of origin	MX

### Contractual warranty

Warranty period	18 months
-----------------	-----------