



Price* : 654.00 USD



8536SCG3V01H200S has not been replaced. Please contact your customer care center for more information.

Main

| | |
|---------------------------|--------------------------|
| Product or component type | Starter |
| Type | S |
| Control Circuit Type | Separate control circuit |

Complementary

| | |
|-------------------------|--|
| Control Circuit Voltage | 24 V AC 60 Hz |
| Motor starter type | Non reversing |
| Line Rated Current | 27 A |
| Number of Poles | 3P |
| Phase | 3 phases |
| Horsepower Rating | 7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC |
| System Voltage | 600 V AC |
| Control Units | No control units |
| Thermal overload type | Solid state Motor Logic class 20 |
| Electrical connection | Screw clamp terminals |
| NEMA size | 1 |

Environment

| | |
|------------------------|----------------------------|
| Enclosure Type | NEMA 1 painted sheet steel |
| Product certifications | CSA NEMA UL listed |

Ordering and shipping details

| | |
|----------|------------------------------------|
| Category | 21192 - 8502,36 SC,SD(NOT S*R,T,W) |
|----------|------------------------------------|

| | |
|-----------------------|-----|
| Discount Schedule | CP1 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 8 |
| Returnability | N |
| Country of origin | MX |

Offer Sustainability

| | |
|------------------------|--|
| RoHS (date code: YYWW) | Will be compliant Will be compliant |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|