

# 8536SCG3V06C6X20

Non-Reversing Starter Size 1, 3-Pole, Melting Alloy Overload, Nema 1 +Options



Price\* : 1,112.00 USD



8536SCG3V06C6X20 has not been replaced. Please contact your customer care center for more information.

## Main

Product or component type	Starter
Type	S
Control Circuit Type	Common control circuit

## Complementary

Control Circuit Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	27 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
System Voltage	600 V AC
Control Units	Selector switch (ON-OFF)
Auxiliary Contacts	2 NO
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	1

## Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	CSA NEMA UL listed

Ordering and shipping details

Category	21192 - 8502,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	6
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant Will be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------