

8536SCG3V06CH10P1

Non-Reversing Starter Size 1, 3-Pole, Motor Logic
SSOLR (Class 10), NEMA 1



Price* : 1,196.00 USD



8536SCG3V06CH10P1 has not been replaced. Please contact your customer care center for more information.

Main

Product or component type	Starter
Type	S
Control Circuit Type	Common control circuit

Complementary

Control Circuit Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	27 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator: on type: incandescent
Thermal overload type	Solid state Motor Logic class 10
Electrical connection	Screw clamp terminals
NEMA size	1

Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	NEMA UL listed CSA

Ordering and shipping details

Category	21192 - 8502,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	7
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------