




Price\* : 653.00 USD



### Main

Product or component type	Starter
Type	S
Control Circuit Type	Common control circuit

### Complementary

Control Circuit Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	27 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Thermal overload type	Solid state Motor Logic class 10
Electrical connection	Screw clamp terminals
NEMA size	1

### Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	NEMA CSA UL listed

## Ordering and shipping details

Category	21192 - 8502,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901340928
Nbr. of units in pkg.	1
Package weight(Lbs)	6
Returnability	N
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Will be compliant Will be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

## Contractual warranty

Warranty period	18 months
-----------------	-----------

## 8536SCG3V06H10 is replaced by:



### 8536S Non-Reversing Starter 8536SCG3V06H30

Non-Reversing Starter Size 1, 3-Pole, Motor Logic SSOLR, NEMA 1

Qty 1

Reason for Substitution: End of life | Substitution date: 01 January 2017