

8536SCG3V07S

Non-Reversing Starter Size 1, 3-Pole, Melting Alloy Overload, Nema 1 +Options

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 590.00 USD



Main

Product or component type	Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	600 V AC 60 Hz 550 V AC 50 Hz
Motor starter type	Non reversing
Line Rated Current	27 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	1
Height	10 in (254 mm)
Depth	5.55 in (141 mm)
Width	5.98 in (152 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	CSA

NEMA
UL listed

Ordering and shipping details

Category	21192 - 8502,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	6
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------