


Price* : 1,956.00 USD



⚠ Discontinued

8536SCG3V84FF4P1P2T has not been replaced.
Please contact your customer care center for more information.

Main

Product or component type	Starter
Type	S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 208 V AC 60 Hz primary circuit
Motor starter type	Non reversing
Line Rated Current	27 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Pilot Light	Red indicator: on type: incandescent Green indicator: off type: incandescent
Control Circuit Fusing	2 fuses (primary), 1 fuse (secondary)
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	1

Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	CSA UL listed NEMA

Ordering and shipping details

Category	21192 - 8502,36 SC,SD(NOT S*R,T,W)
----------	------------------------------------

Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	27.16
Returnability	N
Country of origin	MX

Contractual warranty

Warranty period	18 months
-----------------	-----------