

# Product data sheet

## Characteristics

# 8536SCG3V90CF4TT1X11

## Non-Reversing Starter Size 1, 3-Pole, Melting Alloy Overload, Nema 1 +Options

Price\* : 1,565.00 USD



8536SCG3V90CF4TT1X11 has not been replaced.  
Please contact your customer care center for more information.

⚠ Discontinued

### Main

Product or component type	Starter
Type	S
Control Circuit Type	Common control circuit

### Complementary

Control Circuit Voltage	208 V AC 60 Hz primary circuit 24 V AC 60 Hz secondary circuit
Motor starter type	Non reversing
Line Rated Current	27 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Auxiliary Contacts	1 NO + 1 NC
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	1

### Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	NEMA CSA UL listed

### Ordering and shipping details

Category	21192 - 8502,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1

---

Package weight(Lbs)	31.970000000000002
Returnability	N

---

**Contractual warranty**

---

Warranty period	18 months
-----------------	-----------

---