

# Product data sheet

## Characteristics

# 8536SCG4V06

## Non-Reversing Starter Size 1, 4-Pole, Melting Alloy Overload, Nema 1

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 761.00 USD



### Main

|                           |                        |
|---------------------------|------------------------|
| Product or component type | Starter                |
| Type                      | S                      |
| Control Circuit Type      | Common control circuit |

### Complementary

|                         |  |
|-------------------------|--|
| Control Circuit Voltage | 440 V AC 50 Hz<br>480 V AC 60 Hz                                       |
| Motor starter type      | Non reversing  |
| Line Rated Current      | 27 A   |
| Number of Poles         | 4P   |
| Phase                   | 2 phases   |
| Horsepower Rating       | 7.5 HP 200 V AC<br>7.5 HP 230 V AC<br>10 HP 460 V AC<br>10 HP 575 V AC |
| System Voltage          | 600 V AC   |
| Control Units           | No control units   |
| Thermal overload type   | Melting alloy 2 Thermal Units  |
| Electrical connection   | Screw clamp terminals  |
| NEMA size               | 1  |
| Height                  | 10 in (254 mm)   |
| Depth                   | 5.55 in (141 mm)   |
| Width                   | 5.98 in (152 mm)   |

### Environment

|                        |                            |
|------------------------|----------------------------|
| Enclosure Type         | NEMA 1 painted sheet steel |
| Product certifications | CSA                        |

NEMA  
UL listed

### Ordering and shipping details

|                       |                                    |
|-----------------------|------------------------------------|
| Category              | 21192 - 8502,36 SC,SD(NOT S*R,T,W) |
| Discount Schedule     | CP1                                |
| GTIN                  | 00785901906070                     |
| Nbr. of units in pkg. | 1                                  |
| Package weight(Lbs)   | 6                                  |
| Returnability         | N                                  |
| Country of origin     | MX                                 |

### Offer Sustainability

|                           |  |
|---------------------------|--|
| RoHS (date code: YYWW)    | Will not be compliant<br>Will not be compliant   |
| California proposition 65 | WARNING: This product can expose you to chemicals including:   |
| ----- Substance 1         | Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. |
| ----- More information    | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>                                    |

### Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|