

8536SCH2V03A

Non-Reversing Starter Size 1P, 2-Pole, Melting Alloy Overload, Nema 3R +Options

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 1,203.00 USD



Main

Product or component type	Starter
Type	S
Control Circuit Type	Common control circuit

Complementary

Control Circuit Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	27 A
Number of Poles	2P
Phase	1 phase
Horsepower Rating	3 HP 115 V AC 5 HP 230 V AC
System Voltage	600 V AC
Control Units	2 momentary push-buttons (START-STOP)
Thermal overload type	Melting alloy 1 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	1P
Height	12.28 in (312 mm)
Depth	7.13 in (181 mm)
Width	8.86 in (225 mm)

Environment

Enclosure Type	NEMA 3R painted sheet steel
Product certifications	CSA NEMA UL listed

Ordering and shipping details

Category	21192 - 8502,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	25.289999999999999
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------