

# 8536SCH3V02CS

## Non-Reversing Starter Size 1, 3-Pole, Melting Alloy Overload, Nema 3R +Options

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 1,097.00 USD



### Main

Product or component type	Starter
Type	S
Control Circuit Type	Separate control circuit

### Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	27 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	1
Height	12.28 in (312 mm)
Depth	7.13 in (181 mm)
Width	8.86 in (225 mm)

### Environment

Enclosure Type	NEMA 3R painted sheet steel
Product certifications	CSA

NEMA  
UL listed

### Ordering and shipping details

Category	21192 - 8502,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901351665
Nbr. of units in pkg.	1
Package weight(Lbs)	27.050000000000001
Returnability	N
Country of origin	MX

### Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant <b>Will not be compliant</b>
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------