

Product data sheet

Specifications



NEMA Motor Starter, Type S, nonreversing, Size 1, 27A, 10 HP at 460 VAC, 5 kA SCCR, 3 phase, 3 pole, melting alloy, 208 VAC coil, NEMA 3R

8536SCH3V08

⚠ To be discontinued

⚠ To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Type	Motor starter
Product Range	S
Starter Type	Non reversing

Complementary

Nema Size	1
Rated Current	27 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Melting alloy 3
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
Scrr	Circuit-breaker: 5 kA at 600 V AC Fuse: 5 kA at 600 V AC
Coil Voltage	208 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Terminal Type	Screw clamp terminals
Height	12.28 in (311.91 mm)
Width	8.84 in (224.54 mm)
Depth	7.13 in (181.10 mm)

Environment

Enclosure Type	NEMA 3R painted sheet steel
----------------	-----------------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Certifications	UL Listed CSA NEMA
----------------	--------------------------

Ordering and shipping details

Category	21192 - 8502,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Gtin	785901824596
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.28 in (31.2 cm)
Package 1 Width	8.86 in (22.5 cm)
Package 1 Length	7.13 in (18.1 cm)
Package 1 Weight	13.96 lb(US) (6.332 kg)

Contractual warranty

Warranty	18 months
----------	-----------