

Product data sheet

Specifications

SQUARE D



Non-Reversing Starter Size 1, 3-Pole, Motor Logic SSOLR (Class 10), Open

8536SCO3V01H10S

! Discontinued

Main

Product Type	Starter
Product Range	S
Starter Type	Non reversing

Complementary

Nema Size	1
Rated Current	27 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Solid state Motor Logic class 10
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
Coil Voltage	24 V AC 60 Hz
Control Circuit Type	Separate control circuit
Control Units	No control units
Terminal Type	Screw clamp terminals

Environment

Enclosure Type	Not rated (open device)
Certifications	CSA UL Listed NEMA

Ordering and shipping details

Category	21192-8502,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Gtin	00785901970217
Returnability	No
Country Of Origin	MX

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	5.00 lb(US) (2.268 kg)

Contractual warranty

Warranty	18 months
----------	-----------