

# Product data sheet

Specifications

SQUARE D



## Non-Reversing Starter Size 1, 3-Pole, Motor Logic SSOLR (Class 10), Open

8536SCO3V02H100SX20

Discontinued

### Main

Product Type	Starter
Product Range	S
Starter Type	Non reversing

### Complementary

Nema Size	1
Rated Current	27 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Solid state Motor Logic class 10
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Separate control circuit
Control Units	No control units
Auxiliary Contacts	2 NO
Terminal Type	Screw clamp terminals

### Environment

Enclosure Type	Not rated (open device)
Certifications	NEMA CSA UL Listed

### Ordering and shipping details

Category	21192-8502,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

Warranty	18 months
----------	-----------