

Product data sheet

Characteristics

8536SCO3V02H308SX11

Non-Reversing Starter Size 1, 3-Pole, Motor Logic SSOLR, Open +Options

Product availability : Non-Stock - Not normally stocked in distribution facility

Price* : 965.00 USD



Main

| | |
|---------------------------|--------------------------|
| Product or component type | Starter |
| Type | S |
| Control Circuit Type | Separate control circuit |

Complementary

| | |
|-------------------------|--|
| Control Circuit Voltage | 110 V AC 50 Hz 120 V AC 60 Hz |
| Motor starter type | Non reversing |
| Line Rated Current | 27 A |
| Number of Poles | 3P |
| Phase | 3 phases |
| Horsepower Rating | 7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC |
| System Voltage | 600 V AC |
| Control Units | No control units |
| Auxiliary Contacts | 1 NO + 1 NC |
| Thermal overload type | Solid state Motor Logic class 10/20 |
| Electrical connection | Screw clamp terminals |
| NEMA size | 1 |
| Height | 6.77 in (172 mm) |
| Depth | 4.21 in (107 mm) |
| Width | 4.02 in (102 mm) |

Environment

| | |
|------------------------|--------------------------|
| Enclosure Type | Not rated (open device) |
| Product certifications | NEMA UL listed CSA |

Ordering and shipping details

| | |
|-----------------------|------------------------------------|
| Category | 21192 - 8502,36 SC,SD(NOT S*R,T,W) |
| Discount Schedule | CP1 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 5 |
| Returnability | N |
| Country of origin | MX |

Offer Sustainability

| | |
|----------------------------|--|
| California proposition 65 | WARNING: This product can expose you to chemicals including: |
| - - - - - Substance 1 | Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. |
| - - - - - More information | For more information go to www.p65warnings.ca.gov |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|