


# 8536SCO3V03BSX22

Non-Reversing Starter Size 1, 3-Pole, Ambient Compensated Bimetallic, Open



Price\* : 1,247.00 USD



8536SCO3V03BSX22 has not been replaced. Please contact your customer care center for more information.

## Main

Product or component type	Starter
Type	S
Control Circuit Type	Separate control circuit

## Complementary

Control Circuit Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	27 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Auxiliary Contacts	2 NO + 2 NC
Thermal overload type	Ambient compensated bimetallic
Electrical connection	Screw clamp terminals
NEMA size	1

## Environment

Enclosure Type	Not rated (open device)
Product certifications	UL listed NEMA CSA

Ordering and shipping details

Category	21192 - 8502,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	5
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 <a href="#">Will be compliant on 3Q2014</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>

Contractual warranty

Warranty period	18 months
-----------------	-----------