


# 8536SCR3V02AS

Non-Reversing Starter Size 1, 3-Pole, Thermal - Melting Alloy



Price\* : 3,402.00 USD



8536SCR3V02AS has not been replaced. Please contact your customer care center for more information.

## Main

Product or component type	Starter
Type	S
Control Circuit Type	Separate control circuit

## Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	27 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
System Voltage	600 V AC
Control Units	2 momentary push-buttons (START-STOP)
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	1

## Environment

Enclosure Type	NEMA 7/9 cast aluminium type: spin top
Product certifications	CSA NEMA UL listed

### Ordering and shipping details

Category	21202 - 8502,36 S*R,S*T,S*W
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	19.5
Returnability	N

### Offer Sustainability

RoHS (date code: YYWW)	Will be compliant Will be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

### Contractual warranty

Warranty period	18 months
-----------------	-----------