

Product data sheet

Characteristics

8536SCT43V02AS

Non-Reversing Starter Size 1, 3-Pole, Melting Alloy Overload, NEMA 7/9 +Options

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 2,840.00 USD



Main

Product or component type	Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	27 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
System Voltage	600 V AC
Control Units	2 momentary push-buttons (START-STOP)
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	1
Height	438 mm
Depth	10.98 in (279 mm)
Width	14.25 in (362 mm)

Environment

Enclosure Type	NEMA 7/9 cast aluminium type: bolted
Product certifications	CSA

NEMA
UL listed

Ordering and shipping details

Category	21202 - 8502,36 S*R,S*T,S*W
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	50
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------