

Product data sheet

Specifications



Non-Reversing Starter Size 1, 2-Pole, Melting Alloy Overload, NEMA 4/4X +Options

8536SCW11V02AP1

⚠ Discontinued

Main

Product Type	Starter
Product Range	S
Starter Type	Non reversing

Complementary

Nema Size	1
Rated Current	27 A
Number Of Poles	2P
Maximum Voltage Rating	600 V AC
Phase	1 phase
Type Of Overload	Melting alloy 1
Horsepower Rating	3 HP 230 V AC 2 HP 115 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	2 momentary push-buttons (START-STOP)
Pilot Light	Red indicator on incandescent
Terminal Type	Screw clamp terminals

Environment

Enclosure Type	NEMA 4/4X brushed stainless steel
Certifications	UL Listed CSA NEMA

Ordering and shipping details

Category	21203-8502,36 W/STAINLESS ENCLOSURES
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	34.11 lb(US) (15.472 kg)

Contractual warranty

Warranty	18 months
----------	-----------