

8536SCW11V03AP1

Non-Reversing Starter Size 1, 2-Pole, Melting Alloy Overload, NEMA 4/4X +Options



Price* : 1,722.00 USD



⚠ Discontinued

8536SCW11V03AP1 has not been replaced. Please contact your customer care center for more information.

Main

Product or component type	Starter
Type	S
Control Circuit Type	Common control circuit

Complementary

Control Circuit Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	27 A
Number of Poles	2P
Phase	1 phase
Horsepower Rating	3 HP 230 V AC 2 HP 115 V AC
System Voltage	600 V AC
Control Units	2 momentary push-buttons (START-STOP)
Pilot Light	Red indicator: on type: incandescent
Thermal overload type	Melting alloy 1 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	1

Environment

Enclosure Type	NEMA 4/4X brushed stainless steel
Product certifications	UL listed CSA NEMA

Ordering and shipping details

Category	21203 - 8502,36 W/STAINLESS ENCLOSURES
----------	--

Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	34.109999999999999
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------