


8536SCW13V01H20S

Non-Reversing Starter Size 1, 3-Pole, Motor Logic
SSOLR (Class 20), NEMA 4/4X



Price* : 1,167.00 USD



8536SCW13V01H20S has not been replaced. Please contact your customer care center for more information.

Main

Product or component type	Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	24 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	27 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Thermal overload type	Solid state Motor Logic class 20
Electrical connection	Screw clamp terminals
NEMA size	1

Environment

Enclosure Type	NEMA 4/4X brushed stainless steel
Product certifications	CSA NEMA UL listed

Ordering and shipping details

Category	21203 - 8502,36 W/STAINLESS ENCLOSURES
----------	--

Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	36
Returnability	N

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant Will be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------