


# 8536SCW13V02CP1SX11

Non-Reversing Starter Size 1, 3-Pole, Melting Alloy Overload, NEMA 4/4X +Options

Price\* : 2,084.00 USD



⚠ Discontinued

8536SCW13V02CP1SX11 has not been replaced.  
Please contact your customer care center for more information.

## Main

Product or component type	Starter
Type	S
Control Circuit Type	Separate control circuit

## Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	27 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator: on type: incandescent
Auxiliary Contacts	1 NO + 1 NC
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	1

## Environment

Enclosure Type	NEMA 4/4X brushed stainless steel
Product certifications	CSA NEMA UL listed

## Ordering and shipping details

Category	21203 - 8502,36 W/STAINLESS ENCLOSURES
Discount Schedule	CP1

Nbr. of units in pkg.	1
Package weight(Lbs)	35.939999999999998
Returnability	N
Country of origin	MX

**Contractual warranty**

Warranty period	18 months
-----------------	-----------