

# 8536SCW13V06A16

Non-Reversing Starter Size 1, 3-Pole, Melting Alloy Overload, NEMA 4/4X +Options



Price\* : 1,479.00 USD



8536SCW13V06A16 has not been replaced. Please contact your customer care center for more information.

## Main

Product or component type	Starter
Type	S
Control Circuit Type	Common control circuit

## Complementary

Control Circuit Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	27 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
System Voltage	600 V AC
Control Units	1 maintained push-button (START-STOP)
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	1

## Environment

Enclosure Type	NEMA 4/4X brushed stainless steel
Product certifications	NEMA UL listed CSA

Ordering and shipping details

Category	21203 - 8502,36 W/STAINLESS ENCLOSURES
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	33.579999999999998
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------