

# Product data sheet

## Characteristics

# 8536SCW14V06

## Non-Reversing Starter Size 1, 4-Pole, Melting Alloy Overload, NEMA 4/4X

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 1,301.00 USD



### Main

Product or component type	Starter
Type	S
Control Circuit Type	Common control circuit

### Complementary

Control Circuit Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	27 A
Number of Poles	4P
Phase	2 phases
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Thermal overload type	Melting alloy 2 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	1
Height	13.19 in (335 mm)
Depth	7.8 in (198 mm)
Width	6.38 in (162 mm)

### Environment

Enclosure Type	NEMA 4/4X brushed stainless steel
Product certifications	CSA

NEMA  
UL listed

---

### Ordering and shipping details

Category	21203 - 8502,36 W/STAINLESS ENCLOSURES
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	33.25
Returnability	N
Country of origin	MX

---

### Offer Sustainability

RoHS (date code: YYWW)	Will be compliant Will be compliant
------------------------	--

---

### Contractual warranty

Warranty period	18 months
-----------------	-----------

---