

8536SDW11V84A3F4P21TX11

Non-Reversing Starter Size 2, 3-Pole, Melting Alloy Overload, NEMA 4/4X +Options

Price** : 3,807.00 USD



⚠ Discontinued

8536SDW11V84A3F4P21TX11 has not been replaced.
Please contact your customer care center for more information.

Main

Product or component type	Starter
Type	S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 208 V AC 60 Hz primary circuit
Motor starter type	Non reversing
Line Rated Current	45 A
Number of Poles	2P
Phase	1 phase
Horsepower Rating	10 HP 200 V AC 15 HP 230 V AC 25 HP 460 V AC 25 HP 575 V AC
System Voltage	600 V AC
Control Units	2 momentary push-buttons (ON-OFF)
Pilot Light	Red indicator: on type: incandescent with push-to-test
Auxiliary Contacts	1 NO + 1 NC
Control Circuit Fusing	2 fuses (primary)
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	2

Environment

Enclosure Type	NEMA 4/4X brushed stainless steel
Product certifications	NEMA CSA UL listed

Ordering and shipping details

Category	21203 - 8502,36 W/STAINLESS ENCLOSURES
----------	--

Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	42.539999999999999
Returnability	N
Country of origin	MX

Contractual warranty

Warranty period	18 months
-----------------	-----------