

Product data sheet

Specifications

SQUARE D



Non-Reversing Starter Size 3, 3-Pole, Motor Logic SSOLR (Class 20), NEMA 1

8536SEG1V02CH20P1SX20

Discontinued

Main

Product Type	Starter
Product Range	S
Starter Type	Non reversing

Complementary

Nema Size	3
Rated Current	90 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Solid state Motor Logic class 20
Horsepower Rating	25 HP 200 V AC 30 HP 230 V AC 50 HP 460 V AC 50 HP 575 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Separate control circuit
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator on incandescent
Auxiliary Contacts	2 NO
Terminal Type	Screw clamp terminals

Environment

Enclosure Type	NEMA 1 painted sheet steel
Certifications	UL Listed NEMA CSA

Ordering and shipping details

Category	21193-8502,36 SE,SF(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------