

8536SEW11V81CFF4P1TX11

Non-Reversing Starter Size 3, 3-Pole, Melting Alloy Overload, NEMA 4/4X +Options

Price** : 5,475.00 USD



⚠ Discontinued

8536SEW11V81CFF4P1TX11 has not been replaced.
Please contact your customer care center for more information.

Main

Product or component type	Starter
Type	S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Motor starter type	Non reversing
Line Rated Current	90 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	25 HP 200 V AC 30 HP 230 V AC 50 HP 460 V AC 50 HP 575 V AC
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator: on type: incandescent
Auxiliary Contacts	1 NO + 1 NC
Control Circuit Fusing	2 fuses (primary), 1 fuse (secondary)
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	3

Environment

Enclosure Type	NEMA 4/4X brushed stainless steel
Product certifications	CSA NEMA UL listed

Ordering and shipping details

Category	21203 - 8502,36 W/STAINLESS ENCLOSURES
----------	--

Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	78.590000000000003
Returnability	N
Country of origin	MX

Contractual warranty

Warranty period	18 months
-----------------	-----------