

# Product data sheet

Specifications

SQUARE D



## Non-Reversing Starter Size 4, 3-Pole, Melting Alloy Overload, Open +Options

8536SFO1V02SX22Y342

Discontinued

### Main

Product Type	Starter
Product Range	S
Starter Type	Non reversing

### Complementary

Nema Size	4
Rated Current	135 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Melting alloy 3
Horsepower Rating	40 HP 200 V AC 50 HP 230 V AC 100 HP 460 V AC 100 HP 575 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Separate control circuit
Control Units	No control units
Auxiliary Contacts	2 NO + 2 NC
Terminal Type	Screw clamp terminals

### Environment

Enclosure Type	Not rated (open device)
Certifications	NEMA CSA UL Listed

### Ordering and shipping details

Category	21193-8502,36 SE,SF(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No

### Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months