

# 8536SGA1V02C1H20P1SX30

Non-Reversing Starter Size 5, 3-Pole, Motor Logic SSOLR (Class 20), NEMA 12

Price\*\* : 14,592.00 USD



8536SGA1V02C1H20P1SX30 has not been replaced.  
Please contact your customer care center for more information.

⚠ Discontinued

## Main

Product or component type	Starter
Type	S
Control Circuit Type	Separate control circuit

## Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	270 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	75 HP 200 V AC 100 HP 230 V AC 200 HP 460 V AC 200 HP 575 V AC
System Voltage	600 V AC
Control Units	Selector switch (START-STOP)
Pilot Light	Red indicator: on type: incandescent
Auxiliary Contacts	3 NO
Thermal overload type	Solid state Motor Logic class 20
Electrical connection	Screw clamp terminals
NEMA size	5
Height	47.01 in (1194 mm)
Depth	341 mm
Width	17.2 in (437 mm)

## Environment

Enclosure Type	NEMA 12 painted sheet steel
Product certifications	UL listed NEMA CSA

Ordering and shipping details

Category	21194 - 8502,36SG(NOT S*R,S*T,S*W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	200
Returnability	Y
Country of origin	MX

Contractual warranty

Warranty period	18 months
-----------------	-----------