

Product data sheet

Specifications

SQUARE D



Non-Reversing Starter Size 5, 3-Pole, Motor Logic SSOLR (Class 20), NEMA 1

8536SGG1V02CH20SX11

Price*: 10,970.00 USD

! Discontinued

Main

Product Type	Starter
Product Range	S
Starter Type	Non reversing

Complementary

Nema Size	5
Rated Current	270 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Solid state Motor Logic class 20
Horsepower Rating	75 HP 200 V AC 100 HP 230 V AC 200 HP 460 V AC 200 HP 575 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Separate control circuit
Control Units	Selector switch (HAND-OFF-AUTO)
Auxiliary Contacts	1 NO + 1 NC
Terminal Type	Screw clamp terminals
Height	44.21 in (1123 mm)
Width	17.20 in (437 mm)
Depth	12.95 in (329 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel
Certifications	CSA UL Listed NEMA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	US
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------