

Product data sheet

Characteristics

8536SHO2V06

Non-Reversing Starter Size 6, 3-Pole, Melting Alloy Overload, Open

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 21,756.00 USD



Main

Product or component type	Starter
Type	S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	540 A
Number of Poles	3P
Phase	3 phases
Horsepower Rating	150 HP 200 V AC 200 HP 230 V AC 400 HP 460 V AC 400 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Control Circuit Fusing	2 fuses (primary), 2 fuses (secondary)
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	6
Height	713 mm
Depth	253 mm
Width	10.55 in (268 mm)

Environment

Enclosure Type	Not rated (open device)
----------------	-------------------------

Product certifications	CSA NEMA UL listed
------------------------	--------------------------

Ordering and shipping details

Category	21195 - 8502,36 SH,SJ(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901619796
Nbr. of units in pkg.	1
Package weight(Lbs)	67.42000000000002
Returnability	Y
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant <i>Will not be compliant</i>
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------