

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 2,285.00 USD



Main

Contacteur application	Non-reversing
Device short name	S

Complementary

[Ue] rated operational voltage	600 V AC 60 Hz 550 V AC 50 Hz
Depth	211.84 mm (8.34 in)
Device mounting	Surface
Height	609.60 mm (24 in)
NEMA size	0
Number of poles	3
Number of thermal units required	3
Net weight	18.14 kg (40 lb(US))
Reset	Without external
Width	241.30 mm (9.5 in)

Environment

NEMA degree of protection	NEMA 12
Product certifications	CSA LR584 class 3211 04 UL listed file E152395 CCN NKJH7

Ordering and shipping details

Category	21212 - 8538,39SB(NOT S*R,S*T,S*W)
Discount Schedule	CP1
Package weight(Lbs)	20.41 kg (45 lb(US))
Returnability	No
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
EU RoHS Directive	Will be compliant – Date to be confirmed

Contractual warranty

Warranty	18 months
----------	-----------
