

Product data sheet

Specifications

SQUARE D



NEMA Combination Starter, Type S, nonfusible disconnect, Size 0, 18A, 5 HP at 600 VAC polyphase, 600 VAC coil, NEMA 12

8538SBA11S8V07

To be discontinued

To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| | |
|-----------------------|---------------|
| Contactor Application | Non-reversing |
| Device Short Name | S |

Complementary

| | |
|----------------------------------|----------------------------------|
| [Ue] Rated Operational Voltage | 600 V AC 60 Hz 550 V AC 50 Hz |
| Depth | 8.34 in (211.84 mm) |
| Device Mounting | Surface |
| Height | 24 in (609.60 mm) |
| Nema Size | 0 |
| Number Of Poles | 3 |
| Number Of Thermal Units Required | 3 |
| Net Weight | 40 lb(US) (18.14 kg) |
| Reset | Without external |
| Width | 9.5 in (241.30 mm) |

Environment

| | |
|---------------------------|---|
| Nema Degree Of Protection | NEMA 12 |
| Product Certifications | CSA LR584 class 3211 04 UL listed file E152395 CCN NKJH7 |

Ordering and shipping details

| | |
|-------------------|------------------------------------|
| Category | 21212 - 8538,39SB(NOT S*R,S*T,S*W) |
| Discount Schedule | CP1 |
| Returnability | No |
| Country Of Origin | MX |

Packing Units

| | |
|------------------------------|-----|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------|--------------------------|
| Package 1 Height | 24.02 in (61.0 cm) |
| Package 1 Width | 9.49 in (24.1 cm) |
| Package 1 Length | 8.35 in (21.2 cm) |
| Package 1 Weight | 45.00 lb(US) (20.412 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

| | |
|---------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Not compliant |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |