

Price** : 3,641.00 USD



8538SBA21V80CFF4P1TX22 has not been replaced.
Please contact your customer care center for more information.

Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	240 V AC 60 Hz primary circuit 120 V AC 60 Hz secondary circuit
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	3 hp 230 V AC 3 phases 5 hp 460 V AC 3 phases 5 hp 575 V AC 3 phases 3 hp 200 V AC 3 phases
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator: on type: incandescent
Auxiliary Contacts	2 NO + 2 NC
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Thermal overload type	Melting alloy 3 Thermal Units
Disconnect Type	Non-fusible disconnect switch
NEMA size	0

Environment

Enclosure Type	NEMA 12 painted sheet steel and with external reset
----------------	---

Ordering and shipping details

Category	21212 - 8538,39SB(NOT S*R,S*T,S*W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	45
Returnability	N

Contractual warranty

Warranty period	18 months
-----------------	-----------
