

Product availability : Non-Stock - Not normally stocked in distribution facility

Price** : 3,328.00 USD



Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	3 hp 230 V AC 3 phases 5 hp 460 V AC 3 phases 5 hp 575 V AC 3 phases 3 hp 200 V AC 3 phases
System Voltage	600 V AC
Control Units	No control units
Pilot Light	Red indicator: on type: incandescent Green indicator: off type: incandescent
Auxiliary Contacts	1 NO + 1 NC
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Thermal overload type	Melting alloy 3 Thermal Units
Disconnect Type	Non-fusible disconnect switch
NEMA size	0

Environment

Enclosure Type	NEMA 12 painted sheet steel and with external reset
----------------	---

Ordering and shipping details

Category	21212 - 8538,39SB(NOT S*R,S*T,S*W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	45

Returnability	N
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------