

# Product data sheet

Specifications



## COMBO STARTER 600VAC 18A NEMA

8538SBA43V81CF4P1TX20

Price\*: 3,104.00 USD

⚠ Discontinued

### Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

### Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Starter Type	Non reversing
Number Of Poles	3P
Horsepower Rating	5 hp 460 V AC, 3 phase 5 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch HAND-OFF-AUTO)
Pilot Light	Red indicator on incandescent
Auxiliary Contacts	2 NO
Control Circuit Fusing	2 fuses primary circuit
Thermal Overload Type	Melting alloy 3
Disconnect Type	Fusible disconnect switch R, 30 A
Nema Size	0

### Environment

Enclosure Type	NEMA 12 painted sheet steel with external reset
----------------	---

### Ordering and shipping details

Discount Schedule	CP1
Gtin	785901783985
Returnability	No
Country Of Origin	US

### Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications