

Product data sheet

Specifications



COMBO STARTER 600VAC 18A NEMA

8538SBG11V81CFF4P1TX20

Price*: 2,853.00 USD

! Discontinued

Main

| | |
|----------------------|-----------------------------|
| Product | Combination Starter |
| Type | S |
| Control Circuit Type | Control circuit transformer |

Complementary

| | |
|-------------------------|--|
| Control Circuit Voltage | 120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit |
| Starter Type | Non reversing |
| Number Of Poles | 3P |
| Horsepower Rating | 3 hp 200 V AC, 3 phase 3 hp 230 V AC, 3 phase 5 hp 460 V AC, 3 phase 5 hp 575 V AC, 3 phase |
| Maximum Voltage Rating | 600 V AC |
| Control Units | Selector switch HAND-OFF-AUTO) |
| Pilot Light | Red indicator on incandescent |
| Auxiliary Contacts | 2 NO |
| Control Circuit Fusing | 2 fuses primary circuit 1 fuse secondary circuit |
| Thermal Overload Type | Melting alloy 3 |
| Disconnect Type | Non-fusible disconnect switch |
| Nema Size | 0 |

Environment

| | |
|----------------|--|
| Enclosure Type | NEMA 1 painted sheet steel with external reset |
|----------------|--|

Ordering and shipping details

| | |
|-------------------|-----|
| Discount Schedule | CP1 |
| Returnability | No |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications