

# Product data sheet

Specifications



## COMBO STARTER 600VAC 18A NEMA

8538SBG11V84CFF4H10P1T

! Discontinued

### Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

### Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 208 V AC 60 Hz primary circuit
Starter Type	Non reversing
Number Of Poles	3P
Horsepower Rating	3 hp 200 V AC, 3 phase 3 hp 230 V AC, 3 phase 5 hp 460 V AC, 3 phase 5 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch HAND-OFF-AUTO)
Pilot Light	Red indicator on incandescent
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Thermal Overload Type	Solid state Motor Logic class 10
Disconnect Type	Non-fusible disconnect switch
Nema Size	0

### Environment

Enclosure Type	NEMA 1 painted sheet steel with external reset
----------------	--

### Ordering and shipping details

Category	21212-8538,39SB(NOT S*R,S*T,S*W)
Discount Schedule	CP1
Returnability	No

### Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications