

Price\*\* : 2,853.00 USD



8538SBG11V84CFF4P1TX11 has not been replaced.  
Please contact your customer care center for more information.

ⓘ Discontinued

## Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

## Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 208 V AC 60 Hz primary circuit
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	3 hp 230 V AC 3 phases 5 hp 460 V AC 3 phases 5 hp 575 V AC 3 phases 3 hp 200 V AC 3 phases
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator: on type: incandescent
Auxiliary Contacts	1 NO + 1 NC
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Thermal overload type	Melting alloy 3 Thermal Units
Disconnect Type	Non-fusible disconnect switch
NEMA size	0

## Environment

Enclosure Type	NEMA 1 painted sheet steel and with external reset
----------------	--

## Ordering and shipping details

Category	21212 - 8538,39SB(NOT S*R,S*T,S*W)
Discount Schedule	CP1
GTIN	00785901717485
Nbr. of units in pkg.	1
Package weight(Lbs)	40
Returnability	Y

---

Country of origin	MX
-------------------	----

---

**Contractual warranty**

---

Warranty period	18 months
-----------------	-----------

---