

# Product data sheet

Specifications

SQUARE D



## COMBO STARTER 600VAC 18A NEMA

8538SBG12V84CF4H20P2T

Discontinued

### Main

|                      |                             |
|----------------------|-----------------------------|
| Product              | Combination Starter         |
| Type                 | S                           |
| Control Circuit Type | Control circuit transformer |

### Complementary

|                         |                                                                    |
|-------------------------|--------------------------------------------------------------------|
| Control Circuit Voltage | 120 V AC 60 Hz secondary circuit<br>208 V AC 60 Hz primary circuit |
| Starter Type            | Non reversing                                                      |
| Number Of Poles         | 3P                                                                 |
| Horsepower Rating       | 3 hp 200 V AC, 3 phase<br>3 hp 230 V AC, 3 phase                   |
| Maximum Voltage Rating  | 600 V AC                                                           |
| Control Units           | Selector switch HAND-OFF-AUTO)                                     |
| Pilot Light             | Green indicator off incandescent                                   |
| Auxiliary Contacts      | Without                                                            |
| Control Circuit Fusing  | 2 fuses primary circuit                                            |
| Thermal Overload Type   | Solid state Motor Logic class 20                                   |
| Disconnect Type         | Fusible disconnect switch H, 30 A                                  |
| Nema Size               | 0                                                                  |

### Environment

|                |                                                |
|----------------|------------------------------------------------|
| Enclosure Type | NEMA 1 painted sheet steel with external reset |
|----------------|------------------------------------------------|

### Ordering and shipping details

|                   |                                  |
|-------------------|----------------------------------|
| Category          | 21212-8538,39SB(NOT S*R,S*T,S*W) |
| Discount Schedule | CP1                              |
| Returnability     | No                               |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications