

Price\*\* : 2,577.00 USD



8538SBG13V02CP21P22SX01 has not been replaced.  
Please contact your customer care center for more information.

### Main

Product	Combination Starter
Type	S
Control Circuit Type	Separate control circuit

### Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	5 hp 460 V AC 3 phases 5 hp 575 V AC 3 phases
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Green indicator: off type: incandescent with push-to-test Red indicator: on type: incandescent with push-to-test
Auxiliary Contacts	1 NC
Thermal overload type	Melting alloy 3 Thermal Units
Disconnect Type	Fusible disconnect switch, Type H Fuse, 30 A
NEMA size	0

### Environment

Enclosure Type	NEMA 1 painted sheet steel and with external reset
----------------	--

### Ordering and shipping details

Category	21212 - 8538,39SB(NOT S*R,S*T,S*W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	45
Returnability	N

### Contractual warranty

Warranty period	18 months
-----------------	-----------