


Price\*\* : 2,553.00 USD



8538SBG32V80AFF4H20TX11 has not been replaced.  
Please contact your customer care center for more information.

### Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

### Complementary

Control Circuit Voltage	240 V AC 60 Hz primary circuit 120 V AC 60 Hz secondary circuit
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	3 hp 230 V AC 3 phases 3 hp 200 V AC 3 phases
System Voltage	600 V AC
Control Units	Push-button (START) Push-button (STOP)
Pilot Light	No indicator
Auxiliary Contacts	1 NO + 1 NC
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Thermal overload type	Solid state Motor Logic class 20
Disconnect Type	Fusible disconnect switch, Type R Fuse, 30 A
NEMA size	0

### Environment

Enclosure Type	NEMA 1 painted sheet steel and with external reset
----------------	--

### Ordering and shipping details

Category	21212 - 8538,39SB(NOT S*R,S*T,S*W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	45
Returnability	N

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---